

Tremetrics Oscar 6 Electro-Acoustic Ear



Oscar 6 Electro-Acoustic Ear

Always insures the validity of your hearing conservation program by checking audiometer test accuracy daily. With the portable OSCAR 6 Electro-Acoustic Ear, the operator simply places the earphones on the color-coded couplers and conducts a hearing test. The resulting data provides a permanent, legally acceptable running log to establish that the audiometer is "in calibration." The reliable OSCAR works equally well with manual, automatic and microprocessor audiometers.

When used with Tremetrics audiometers, the unit performs an accelerated test which speeds up compliance with the OSHA required daily functional check. The patent-pending ID Wizard even generates an automatic compliance record when used with the new HT Wizard audiometer.

Check the extra value features

- proven design fits all standard earphones and easily accommodates Audiocups sound-attenuating earphone enclosures
- color-coded earphone couplers assure proper setup
- portable and extremely easy to operate
- continuous power monitoring with low battery indicator light
- Convenient, tool-free access for 9-volt battery installation.

For more information or a quote, please contact:

Jim Kurzec

Workplace INTEGRA, Inc.

420-B Gallimore Dairy Road

Greensboro, NC 27409

1-888-WPI-0001

jkurzec@wpintegra.com
